



Ball valve actuator unit VZBA-4"-WW-63-T-22-F10-V4V4T-PS240-R-90-4-C

Part number: 1774113

FESTO



Data sheet

Feature	Value
Structural design	2-way ball valve Quarter turn actuator
Actuation type	Pneumatic
Mounting position	Any
Type of mounting	Line installation
Fitting connection	Weld-on ends/weld-on ends
Switching position indication	Slot direction = flow direction
Nominal width DN	100
Operating pressure	6 bar...8.4 bar
Nominal pressure of fitting PN	63
Medium	Compressed air as per ISO 8573-1:2010 [:-:-:-] Inert gas Water – no water vapor Neutral liquids
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Temperature of medium	-10 °C...200 °C
Ambient temperature	-10 °C...80 °C
Flow rate Kv	1414 m³/h
Max. surface temperature of assembly	TX
Explosion group of assembly	IIC, IIIC
Note on materials	RoHS-compliant
LABS (PWIS) conformity	VDMA24364 zone III
Housing material	High-alloy stainless steel
Material number of housing	1.4408
Seals material	PTFE PTFE-reinforced
Ball material	High-alloy stainless steel
Material number for ball	1.4408
Shaft material	High-alloy stainless steel
Material number for shaft	1.4401
Product weight	33500 g

Feature	Value
Explosion prevention and protection	Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX)
Explosive ambient temperature	-10°C ≤ Ta ≤ +60°C
Corrosion resistance class (CRC)	3 - High corrosion stress