

ISO cylinder DSBF-C-63- -PPVA-N3-R

Part number: 1775324

FESTO



Data sheet

Feature	Value
Stroke	1 mm...2800 mm
Piston diameter	63 mm
Piston rod thread	M16x1.5
Cushioning	Pneumatic cushioning, adjustable at both ends
Mounting position	Any
Conforms to standard	ISO 15552
Piston rod end	External thread
Structural design	Piston Piston rod Profile barrel
Position sensing	For proximity sensor
Operating pressure	0.04 MPa...1.2 MPa 0.4 bar...12 bar
Mode of operation	Double-acting
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	3 - High corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-20 °C...80 °C
Impact energy in the end positions	1.3 J
Cushioning length	22 mm
Theoretical force at 6 bar, retracting	1682 N
Theoretical force at 6 bar, advancing	1870 N
Moving mass at 0 mm stroke	460 g
Additional moving mass per 10 mm stroke	25 g
Basic weight with 0 mm stroke	1803 g
Additional weight per 10 mm stroke	65 g
Type of mounting	With internal thread With accessories Optionally:
Pneumatic connection	G3/8
Note on materials	RoHS-compliant
Cover material	Die-cast aluminum, coated

Feature	Value
Piston seal material	TPE-U(PU)
Material of piston	Wrought aluminum alloy
Piston rod material	High-alloy stainless steel
Piston rod wiper material	TPE-U(PU)
Buffer seal material	TPE-U(PU)
Cushion piston material	POM
Material of cylinder barrel	Wrought aluminum alloy, anodized
Nut material	High-alloy stainless steel
Material of bearing	POM
Flange screws material	Steel, galvanized