

# ISO cylinder DSBF-C-80- -PPVA-N3-R

Part number: 1778184

**FESTO**



## Data sheet

| Feature                                  | Value                                                              |
|------------------------------------------|--------------------------------------------------------------------|
| Stroke                                   | 1 mm...2800 mm                                                     |
| Piston diameter                          | 80 mm                                                              |
| Piston rod thread                        | M20x1.5                                                            |
| Cushioning                               | Pneumatic cushioning, adjustable at both ends                      |
| Mounting position                        | Any                                                                |
| Conforms to standard                     | ISO 15552                                                          |
| Piston rod end                           | External thread                                                    |
| Structural design                        | Piston<br>Piston rod<br>Profile barrel                             |
| Position sensing                         | For proximity sensor                                               |
| Operating pressure                       | 0.04 MPa...1.2 MPa<br>0.4 bar...12 bar                             |
| Mode of operation                        | Double-acting                                                      |
| Operating medium                         | Compressed air as per ISO 8573-1:2010 [7:4:4]                      |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC)         | 3 - High corrosion stress                                          |
| LABS (PWIS) conformity                   | VDMA24364-B2-L                                                     |
| Ambient temperature                      | -20 °C...80 °C                                                     |
| Impact energy in the end positions       | 1.8 J                                                              |
| Cushioning length                        | 31 mm                                                              |
| Theoretical force at 6 bar, retracting   | 2721 N                                                             |
| Theoretical force at 6 bar, advancing    | 3016 N                                                             |
| Moving mass at 0 mm stroke               | 800 g                                                              |
| Additional moving mass per 10 mm stroke  | 39 g                                                               |
| Basic weight with 0 mm stroke            | 3131 g                                                             |
| Additional weight per 10 mm stroke       | 95 g                                                               |
| Type of mounting                         | With internal thread<br>With accessories<br>Optionally:            |
| Pneumatic connection                     | G3/8                                                               |
| Note on materials                        | RoHS-compliant                                                     |
| Cover material                           | Die-cast aluminum, coated                                          |

| Feature                     | Value                            |
|-----------------------------|----------------------------------|
| Piston seal material        | TPE-U(PU)                        |
| Material of piston          | Wrought aluminum alloy           |
| Piston rod material         | High-alloy stainless steel       |
| Piston rod wiper material   | TPE-U(PU)                        |
| Buffer seal material        | TPE-U(PU)                        |
| Cushion piston material     | POM                              |
| Material of cylinder barrel | Wrought aluminum alloy, anodized |
| Nut material                | High-alloy stainless steel       |
| Material of bearing         | POM                              |
| Flange screws material      | Steel, galvanized                |