


# ISO cylinder

## DSBF-C-100-320-PPVA-N3-R

Part number: 1782262

FESTO



## Data sheet

| Feature                                  | Value  |
|--|--|
| Stroke                                   | 320 mm   |
| Piston diameter                          | 100 mm   |
| Piston rod thread                        | M20x1.5  |
| Cushioning                               | Pneumatic cushioning, adjustable at both ends                      |
| Mounting position                        | Any  |
| Conforms to standard                     | ISO 15552  |
| Piston rod end                           | External thread  |
| Structural design                        | Piston<br>Piston rod<br>Profile barrel                             |
| Position sensing                         | For proximity sensor   |
| Operating pressure                       | 0.04 MPa...1.2 MPa<br>0.4 bar...12 bar                             |
| Mode of operation                        | Double-acting  |
| Operating medium                         | Compressed air as per ISO 8573-1:2010 [7:4:4]                      |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC)         | 3 - High corrosion stress  |
| LABS (PWIS) conformity                   | VDMA24364-B2-L   |
| Ambient temperature                      | -20 °C...80 °C   |
| Impact energy in the end positions       | 2.5 J  |
| Cushioning length                        | 31 mm  |
| Theoretical force at 6 bar, retracting   | 4418 N   |
| Theoretical force at 6 bar, advancing    | 4712 N   |
| Moving mass                              | 2293 g   |
| Moving mass at 0 mm stroke               | 1045 g   |
| Additional moving mass per 10 mm stroke  | 39 g   |
| Product weight                           | 7943 g   |
| Basic weight with 0 mm stroke            | 4551 g   |
| Additional weight per 10 mm stroke       | 106 g  |
| Type of mounting                         | With internal thread<br>With accessories<br>Optionally:            |
| Pneumatic connection                     | G1/2   |

| Feature                     | Value                            |
|-----------------------------|----------------------------------|
| Note on materials           | RoHS-compliant                   |
| Cover material              | Die-cast aluminum, coated        |
| Piston seal material        | TPE-U(PU)                        |
| Material of piston          | Wrought aluminum alloy           |
| Piston rod material         | High-alloy stainless steel       |
| Piston rod wiper material   | TPE-U(PU)                        |
| Buffer seal material        | TPE-U(PU)                        |
| Cushion piston material     | POM                              |
| Material of cylinder barrel | Wrought aluminum alloy, anodized |
| Nut material                | High-alloy stainless steel       |
| Material of bearing         | POM                              |
| Flange screws material      | Steel, galvanized                |