

Rotary actuator DRVS-8-90-P

Part number: 1845708

FESTO



Data sheet

| Feature | Value |
|--|--|
| Size | 8 |
| Cushioning angle | 0.5 deg |
| Swivel angle | 0 deg...90 deg |
| Permissible stop radius | 10 mm |
| Cushioning | Elastic cushioning rings/pads at both ends |
| Mounting position | Any |
| Mode of operation | Double-acting |
| Structural design | Rotary vane |
| Position sensing | For proximity sensor |
| Variants | Spigot shaft |
| Operating pressure | 0.35 MPa...0.8 MPa 3.5 bar...8 bar |
| Max. swivel frequency at 6 bar | 3 Hz |
| Repetition accuracy | 1 deg |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC) | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Cleanroom class | Class 6 according to ISO 14644-1 |
| Ambient temperature | 0 °C...60 °C |
| Max. stop force | 30 N |
| Max. axial force | 10 N |
| Max. radial force | 20 N |
| Theoretical torque at 6 bar | 0.35 Nm |
| Permissible mass moment of inertia | 0.0013 kgm ² |
| Product weight | 68 g |
| Type of mounting | With internal thread |
| Pneumatic connection | M3 |
| Note on materials | RoHS-compliant |
| Drive shaft material | High-alloy stainless steel |
| Seals material | TPE-U(PU) |

| Feature | Value |
|------------------|----------------------------------|
| Housing material | Wrought aluminum alloy, anodized |