

ISO cylinder CRDNGS-32- -PPV-A-S6

Part number: 185300

FESTO



Data sheet

Feature	Value
Stroke	10 mm...2000 mm
Piston diameter	32 mm
Piston rod thread	M10x1.25
Based on norm	ISO 15552
Cushioning	Pneumatic cushioning, adjustable at both ends
Mounting position	Any
Piston rod end	External thread
Structural design	Piston Piston rod Pivoting clevis Tie rod Cylinder barrel
Position sensing	For proximity sensor
Variants	End cap with swiveling rod eye Heat-resistant seals max. 120°C
Operating pressure	0.06 MPa...1 MPa 0.6 bar...10 bar
Mode of operation	Double-acting
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	4 - Particularly high corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
For use in the food industry	See supplementary material information
Ambient temperature	0 °C...120 °C
Cushioning length	19 mm
Theoretical force at 6 bar, retracting	415 N
Theoretical force at 6 bar, advancing	483 N
Moving mass at 0 mm stroke	154 g
Additional moving mass per 10 mm stroke	9 g
Basic weight with 0 mm stroke	1104 g
Additional weight per 10 mm stroke	25 g
Type of mounting	With internal thread With accessories Optionally:

Feature	Value
Pneumatic connection	G1/8
Cover material	Cast stainless steel
Seals material	FPM
Housing material	High-alloy stainless steel
Material of piston	Wrought aluminum alloy
Piston rod material	High-alloy stainless steel
Material of cylinder barrel	High-alloy stainless steel
Nut material	High-alloy stainless steel
Material of bearing	Metal polymer compound
Collar nut material	High-alloy stainless steel
Tie rod material	High-alloy stainless steel