

# Short-stroke cylinder AEVC-16-5-I-P-A

Part number: 188096

**FESTO**



## Data sheet

| Feature  | Value  |
|--|--|
| Stroke   | 5 mm   |
| Piston diameter  | 16 mm  |
| Spring resetting force with piston rod in retracted position | 5 N  |
| Cushioning   | Elastic cushioning rings/pads at both ends                         |
| Mounting position  | Any  |
| Mode of operation  | Pushing<br>Single-acting   |
| Structural design  | Piston<br>Piston rod   |
| Position sensing   | For proximity sensor   |
| Operating pressure   | 0.15 MPa...1 MPa<br>1.5 bar...10 bar<br>21.75 psi...145 psi        |
| Operating medium   | Compressed air as per ISO 8573-1:2010 [7:4:4]                      |
| Information on operating and pilot media                     | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC)                             | 1 - Low corrosion stress   |
| LABS (PWIS) conformity                                       | VDMA24364-B1/B2-L  |
| Ambient temperature  | -20 °C...80 °C   |
| Theoretical force at 6 bar, advancing                        | 112 N  |
| Moving mass  | 15 g   |
| Product weight   | 76 g   |
| Type of mounting   | With through-hole<br>With accessories<br>Optionally:               |
| Pneumatic connection   | M5   |
| Note on materials  | RoHS-compliant   |
| Cover material   | Wrought aluminum alloy<br>Anodized                                 |
| Seals material   | TPE-U(PU)  |
| Housing material   | Wrought aluminum alloy<br>Anodized                                 |
| Piston rod material  | High-alloy steel   |