


Short-stroke cylinder

AEVC-16-5-I-P

Part number: 188099

FESTO



Data sheet

Feature	Value
Stroke	5 mm
Piston diameter	16 mm
Spring resetting force with piston rod in retracted position	5 N
Cushioning	Elastic cushioning rings/pads at both ends
Mounting position	Any
Mode of operation	Pushing Single-acting
Structural design	Piston Piston rod
Position sensing	None
Operating pressure	0.15 MPa...1 MPa 1.5 bar...10 bar 21.75 psi...145 psi
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-20 °C...80 °C
Theoretical force at 6 bar, advancing	115 N
Moving mass	8 g
Product weight	33 g
Type of mounting	With through-hole With accessories Optionally:
Pneumatic connection	M5
Note on materials	RoHS-compliant
Cover material	Wrought aluminum alloy Anodized
Seals material	NBR TPE-U(PU)
Housing material	Wrought aluminum alloy Anodized
Piston rod material	High-alloy steel