

# Vacuum suction cup holder

## ESH-HF-2-M10X1

Part number: 189261

FESTO



### Data sheet

Feature	Value
Suction cup holder height compensator	2.6 mm
Nominal width	2 mm
Volume	0.09 cm <sup>3</sup>
Mounting position	Vertical
Structural design	Vacuum connection at top with height compensation
Classification of suction cup holder	Size 2
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7:::-]
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-A1-L
Ambient temperature	-10 °C...60 °C
Product weight	14 g
Type of mounting	With external thread Via vacuum connection
Suction cup mounting	Diameter 4 mm
Vacuum connection	M10x1
Note on materials	RoHS-compliant
Seals material	NBR POM
Retainer bracket material	Tempered steel