


# Short-stroke cylinder ADVC-63-10-I-P-A

Part number: 188284

**FESTO**



## Data sheet

| Feature                                  | Value  |
|--|--|
| Stroke                                   | 10 mm  |
| Piston diameter                          | 63 mm  |
| Based on norm                            | ISO 6431<br>Hole pattern<br>VDMA 24562                             |
| Cushioning                               | Elastic cushioning rings/pads at both ends                         |
| Mounting position                        | Any  |
| Mode of operation                        | Double-acting  |
| Structural design                        | Piston<br>Piston rod   |
| Position sensing                         | For proximity sensor   |
| Operating pressure                       | 0.06 MPa...1 MPa<br>0.6 bar...10 bar<br>8.7 psi...145 psi          |
| Operating medium                         | Compressed air as per ISO 8573-1:2010 [7:4:4]                      |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC)         | 1 - Low corrosion stress   |
| LABS (PWIS) conformity                   | VDMA24364-B1/B2-L  |
| Ambient temperature                      | -20 °C...80 °C   |
| Theoretical force at 6 bar, retracting   | 1750 N   |
| Theoretical force at 6 bar, advancing    | 1870 N   |
| Moving mass                              | 150 g  |
| Moving mass at 0 mm stroke               | 142 g  |
| Additional moving mass per 10 mm stroke  | 16 g   |
| Product weight                           | 640 g  |
| Basic weight with 0 mm stroke            | 626 g  |
| Additional weight per 10 mm stroke       | 74 g   |
| Type of mounting                         | With through-hole<br>With accessories<br>Optionally:               |
| Pneumatic connection                     | G1/8   |
| Note on materials                        | RoHS-compliant   |
| Cover material                           | Wrought aluminum alloy<br>Anodized                                 |

| Feature             | Value                              |
|---------------------|------------------------------------|
| Seals material      | TPE-U(PU)                          |
| Housing material    | Wrought aluminum alloy<br>Anodized |
| Piston rod material | High-alloy steel                   |