

# Vacuum suction cup

## ESS-100-EN

Part number: 189362

FESTO



## Data sheet

Feature	Value
Min. workpiece radius	200 mm
Nominal width	6 mm
Suction cup diameter	100 mm
Suction cup volume	84.66 cm <sup>3</sup>
Connection position	Top
Mounting position	Any
Classification of suction cup holder	Size 5
Suction cup shape	Round, extra-deep
Operating pressure	-95 kPa...0 kPa -0.95 bar...0 bar -13.775 psi...0 psi
Nominal operating pressure	-70 kPa -0.7 bar -10.15 psi
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7:::-]
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-A1-L
For use in the food industry	See supplementary material information
Ambient temperature	-10 °C...70 °C
Holding force at nominal operating pressure	440.8 N
Lateral force at nominal operating pressure	351 N
Product weight	228 g
Type of mounting	Via vacuum connection
Vacuum connection	M10
Color	Black
Shore hardness	60 +/- 5
Material of screwed plug	POM Steel, nickel-plated Steel, galvanized and chrome-plated
Note on materials	RoHS-compliant
Suction cup material	NBR