


Tandem cylinder DNCT-125- -PPV-A-S6

Part number: 191216

FESTO



Data sheet

Feature	Value
Stroke	3 mm...500 mm
Piston diameter	125 mm
Based on norm	ISO 15552 (previously also VDMA 24562, ISO 6431, NF E49 003.1, UNI 10290)
Cushioning	Pneumatic cushioning, adjustable at both ends
Mounting position	Any
Mode of operation	Double-acting
Piston rod end	External thread
Structural design	Piston Piston rod Profile barrel
Position sensing	For proximity sensor
Variants	Heat-resistant seals max. 120°C
Operating pressure	0.06 MPa...1 MPa 0.6 bar...10 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-20 °C...120 °C
Impact energy in the end positions	5 J
Cushioning length	42 mm
Theoretical force at 6 bar, retracting	13762 N
Theoretical force at 6 bar, advancing	14244 N
Type of mounting	With accessories
Pneumatic connection	G1/2
Note on materials	RoHS-compliant
Cover material	Die-cast aluminum
Seals material	FPM
Housing material	Wrought aluminum alloy Smooth anodized
Piston rod material	High-alloy steel