


Tandem cylinder DNCT-4'''- -PPV-A

Part number: 191229



Data sheet

Feature	Value
Stroke	3 mm...500 mm
Based on norm	ISO 15552 (previously also VDMA 24562, ISO 6431, NF E49 003.1, UNI 10290)
Cushioning	Pneumatic cushioning, adjustable at both ends
Mode of operation	Double-acting
Operating pressure	0.06 MPa...1 MPa 0.6 bar...10 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Cushioning length	32 mm
Pneumatic connection	1/2 NPT
Note on materials	RoHS-compliant
Cover material	Die-cast aluminum
Seals material	NBR TPE-U(PU)
Housing material	Wrought aluminum alloy
Piston rod material	High-alloy steel