


Tandem cylinder DNCT-1 1/4"" - -PPV-A-S6

Part number: 191217



Data sheet

| Feature | Value |
|--|---|
| Stroke | 2 mm...500 mm |
| Based on norm | ISO 15552 (previously also VDMA 24562, ISO 6431, NF E49 003.1, UNI 10290) |
| Cushioning | Pneumatic cushioning, adjustable at both ends |
| Mode of operation | Double-acting |
| Operating pressure | 0.06 MPa...1 MPa 0.6 bar...10 bar |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Cushioning length | 20 mm |
| Basic weight with 0 mm stroke | 870 g |
| Pneumatic connection | 1/8 NPT |
| Note on materials | RoHS-compliant |
| Cover material | Die-cast aluminum |
| Seals material | FPM |
| Housing material | Wrought aluminum alloy |
| Piston rod material | High-alloy stainless steel |