


Air reservoir VZS-20-B

Part number: 192161

FESTO



Data sheet

| Feature | Value |
|--|---|
| Volume | 20 l |
| Mounting position | Condensate drain downwards |
| Conforms to standard | EN 286-1 |
| Operating pressure | -0.095 MPa...1.6 MPa -0.95 bar...16 bar -13.775 psi...232 psi |
| CE marking (see declaration of conformity) | as per EU simple pressure vessel directive |
| Operating medium | Compressed air as per ISO 8573-1:2010 [·:·:·] Nitrogen |
| Corrosion resistance class (CRC) | 4 - Particularly high corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Temperature of medium | -10 °C...100 °C |
| Ambient temperature | -10 °C...100 °C |
| Max. tightening torque for connecting thread | 130 Nm |
| Max. tightening torque for condensate drain | 27 Nm |
| Product weight | 9000 g |
| Type of mounting | With through-hole |
| Condensate drain connection | G3/8 |
| Pneumatic connection | G1 |
| Air reservoir material | Steel, powder-coated |