

# Valve manifold

## VDMA-01/02

Part number: 191403


FESTO

Type 14, with standard valves to ISO 15407/-1.

To configure first add product to the shopping basket.

Depending on configuration, the technical data given on the data sheet and the relevant accessories might not match exactly for this product.

Type to be discontinued. Available until 2009.



Exemplary representation

## Data sheet

~ConfIndependentDatasheet

Feature	Value
Valve function	2x3/2 open/closed, single solenoid 2x3/2 closed, single solenoid 2x3/2 open, single solenoid 5/2 single solenoid 5/2 bistable 5/2 bistable-dominant 5/3 pressurized 5/3 exhausted 5/3 closed
Standard nominal flow rate	440 ... 1,000 l/min
Working pressure	-0.9 ... 16 bar
Electrical connection	Individual connection
Max. number of valve positions	16
Ambient temperature	-10 ... 60 °C
Width	18 mm 26 mm
Protection class	IP65
Exhaust-air function	throttleable
Type of actuation	electrical
Valve manifold type	14
Design structure	Piston slide
Pilot air supply	external Internal
Valve manifold structure	modular and expandable
Pilot pressure	3 ... 10 bar
Nominal operating voltage, AC	24 V
Nominal operating voltage DC	12 V 24 V
CE symbol (see declaration of conformity)	according to EU low voltage guideline
Medium temperature	-10 ... 60 °C