

Vacuum generator VN-14-H-T4-PQ2-VA5-RQ3

Part number: 193520

FESTO



Data sheet

Feature	Value
Nominal width of Laval nozzle	1.4 mm
Width dimension	18 mm
Mounting position	Any
Ejector characteristics	High vacuum Standard
Structural design	T-shape
Operating pressure for max. suction rate	5.1 bar
Operating pressure	1 bar...8 bar
Operating pressure for max. vacuum	5 bar
Max. vacuum	88 %
Nominal operating pressure	6 bar
Max. suction rate with respect to atmosphere	51.6 l/min
Air supply time at nominal operating pressure	0.5 s
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication not possible
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Temperature of medium	0 °C...60 °C
Ambient temperature	0 °C...60 °C
Max. tightening torque	0.5 Nm
Product weight	33 g
Type of mounting	With through-hole With accessories
Pneumatic connection 1	QS-6
Pneumatic connection 3	QS-8
Vacuum connection	G1/4
Material of connecting thread	Wrought aluminum alloy
Note on materials	RoHS-compliant
Seals material	NBR
Female nozzle material	POM
Housing material	POM-reinforced
Material of jet nozzle	Wrought aluminum alloy

Feature	Value
Material of pneumatic fitting	Brass Nickel-plated