

ISO cylinder ESNU-25- -

Part number: 194001

FESTO



Data sheet

Feature	Value
Stroke	1 mm...50 mm
Piston diameter	25 mm
Cushioning	Elastic cushioning rings/pads at both ends
Mounting position	Any
Conforms to standard	CETOP RP 52 P ISO 6432
Structural design	Piston Piston rod Cylinder barrel
Position sensing	For proximity sensor
Variants	Extended external thread piston rod Internal thread on piston rod Special thread on piston rod Piston rod with external thread shortened at one end Extended piston rod Axial supply port Piston rod at one end
Operating pressure	0.12 MPa...1 MPa 1.2 bar...10 bar
Mode of operation	Pushing Single-acting
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-20 °C...120 °C
Impact energy in the end positions	0.3 J
Theoretical force at 6 bar, advancing	248 N...261 N
Moving mass at 0 mm stroke	71 g
Additional moving mass per 10 mm stroke	6 g
Basic weight with 0 mm stroke	238 g
Additional weight per 10 mm stroke	11 g
Type of mounting	With accessories
Pneumatic connection	G1/8

Feature	Value
Note on materials	RoHS-compliant
Cover material	Wrought aluminum alloy
Piston rod material	High-alloy stainless steel
Material of cylinder barrel	High-alloy stainless steel