

Round cylinder ESNU-63- -

Part number: 194005

FESTO



Data sheet

Feature	Value
Stroke	1 mm...50 mm
Piston diameter	63 mm
Cushioning	Elastic cushioning rings/pads at both ends
Mounting position	Any
Structural design	Piston Piston rod Cylinder barrel
Position sensing	For proximity sensor
Variants	Increased chemical resistance Extended external thread piston rod Internal thread on piston rod Special thread on piston rod Piston rod with external thread shortened at one end Extended piston rod Axial supply port Uniform, slow movement Low friction Piston rod at one end
Operating pressure	0.12 MPa...1 MPa 1.2 bar...10 bar
Mode of operation	Pushing Single-acting
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-20 °C...120 °C
Theoretical force at 6 bar, advancing	1668 N...1703 N
Moving mass at 0 mm stroke	459 g
Additional moving mass per 10 mm stroke	25 g
Basic weight with 0 mm stroke	1445 g
Additional weight per 10 mm stroke	44 g
Type of mounting	With accessories
Pneumatic connection	G3/8
Note on materials	RoHS-compliant

Feature	Value
Cover material	Wrought aluminum alloy
Seals material	NBR TPE-U(PU)
Piston rod material	High-alloy steel
Material of cylinder barrel	High-alloy stainless steel