

Rod eye
CRSGS-M16X1,5
Part number: 195584

FESTO



Data sheet

Feature	Value
Size	M16x1.5
Corrosion resistance class (CRC)	3 - High corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Suitability for the production of Li-ion batteries	Metals with more than 5% by mass of copper, zinc or nickel by mass are excluded from use. Exceptions are nickel in steel, chemically nickel-plated surfaces, printed circuit boards, cables, electrical plug connectors and coils
Ambient temperature	-40 °C...150 °C
Max. load capacity	4 kN
Product weight	265 g
Note on materials	RoHS-compliant
Material of outer ring	High-alloy steel
Housing material	High-alloy steel
Inner raceway material	High-alloy steel
Nut material	High-alloy steel