

Flat cylinder
DZF-1 5/8"-12"-A-P-A
Part number: 194219

FESTO



Data sheet

Feature	Value
Stroke	12 in
Piston diameter	1 5/8"
Max. angle of rotation of the piston rod +/-	0.6 deg
Cushioning	Elastic cushioning rings/pads at both ends
Mode of operation	Double-acting
Protection against torsion/guide	Oval piston
Operating pressure	0.1 MPa...1 MPa 1 bar...10 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-20 °C...80 °C
Theoretical force at 6 bar, retracting	633 N
Theoretical force at 6 bar, advancing	754 N
Moving mass at 0 mm stroke	120 g
Additional moving mass per 10 mm stroke	9 g
Additional weight per 10 mm stroke	16 g
Basic weight with 0 mm stroke	480 g
Pneumatic connection	1/8 NPT
Cover material	Aluminum
Seals material	FPM TPE-U(PU)
Housing material	Wrought aluminum alloy
Piston rod material	High-alloy steel