

# Plastic tubing PUN-H-12X2-BL

Part number: 197387

**FESTO**



## Data sheet

Feature	Value
Outside diameter	12 mm
Bending radius relevant for flow rate	62 mm
Inside diameter	8 mm
Min. bending radius	33 mm
Application note	TPE-U Ether based
Tubing characteristics	Suitable for energy chains
Operating pressure for entire temperature range	-0.095 MPa...0.6 MPa -0.95 bar...6 bar -13.775 psi...87 psi
Temperature-dependent operating pressure	-0.095 MPa...1 MPa -0.95 bar...10 bar -13.775 psi...145 psi
Information on operating pressure	Water: temperature-dependent operating pressure, see diagram, max. 0.3 MPa at 0 - 60 °C
Certification	German Technical Control Board (TÜV)
Certificate issuing authority	B 013277 0506 00
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-] Water (liquid, ice-free)
Material fire test	UL94 HB
LABS (PWIS) conformity	VDMA24364-B2-L
Suitability for the production of Li-ion batteries	Product corresponds to Festo's internal product definition for use in battery production: Metals with more than 1% by mass of copper, zinc or nickel are excluded from use. The exceptions are nickel in steel, chemically nickel-plated surfaces, circuit boards, cables, electrical plug connectors and coils
Cleanroom class	Statically installed element, no meaningful evaluation possible according to ISO 14644-1
For use in the food industry	See supplementary material information
Ambient temperature	-35 °C...60 °C
Product weight by length	0.0729 kg/m
Pneumatic connection	For plug connection outside diameter 12 mm
Color	Blue
Shore hardness	D 52 +/-3
Note on materials	RoHS-compliant

Feature	Value
Material of pneumatic tubing	TPE-U(PU)