


Axial kit
EAMM-A-S62-80G-G2
Part number: 197 2530



Data sheet

Feature	Value
Nominal length	81 mm
Mounting position	Any
Max. rotational speed	6000 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95 %
Degree of protection	IP40
Ambient temperature	-10 °C...60 °C
Mass moment of inertia	34.8 kgmm ²
Transferable torque	17 Nm
Product weight	1180 g
Interface code, actuator	S62
Interface code, motor in	80G
Note on materials	RoHS-compliant