


Axial kit
EAMM-A-D32-60P-S1
Part number: 2234020



Data sheet

Feature	Value
Nominal length	60.7 mm
Mounting position	Any
Max. rotational speed	8000 rpm
LABS (PWIS) conformity	VDMA24364 zone III
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95 %
Degree of protection	IP65
Ambient temperature	-10 °C...60 °C
Mass moment of inertia	5.87 kgmm ²
Transferable torque	6.5 Nm
Product weight	410 g
Interface code, actuator	D32
Interface code, motor in	60P
Note on materials	RoHS-compliant