


Axial kit
EAMM-A-D60-60G-S1
Part number: 2256698



Data sheet

Feature	Value
Nominal length	83.4 mm
Mounting position	Any
Max. rotational speed	6000 rpm
LABS (PWIS) conformity	VDMA24364 zone III
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95 %
Degree of protection	IP65
Ambient temperature	-10 °C...60 °C
Mass moment of inertia	34.8 kgmm ²
Transferable torque	17 Nm
Product weight	1250 g
Interface code, actuator	D60
Interface code, motor in	60G
Note on materials	RoHS-compliant