

Pneumatic valve VOFD-L35T-

Part number: 2956784

FESTO



Data sheet

Feature	Value
Valve function	3/2, closed, monostable, semi-automatic 3/2, closed, monostable
Actuation type	Electrical
Width	51 mm
Normal nominal flow rate (normalized to DIN 1343)	406 l/min
Pneumatic working port	G1/4 1/4 NPT
Operating pressure	0 MPa...0.8 MPa 0 bar...8 bar 0 psi...116 psi
Structural design	Directly controlled poppet valve
Reset method	Mechanical spring
Degree of protection	IP65
Nominal width	3.5 mm
Sealing principle	Soft
Mounting position	Any
Manual override	Detenting None Non-detenting
Type of control	Direct
Flow direction	Non-reversible
Suitability for vacuum	no
b-value	0.15
C value	1.8 l/sbar
Flow rate for piston valve pressurization	0.32 m³/h
Flow rate for piston valve exhausting	0.32 m³/h
Standard nominal flow rate 2-3	440 l/min
Switching time off	60 ms
On switching time	40 ms
Explosion prevention and protection	Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX)

Feature	Value
Operating medium	Compressed air according to ISO 8573-1:2010 [7:1:2] Compressed air as per ISO 8573-1:2010 [7:2:2]
Corrosion resistance class (CRC)	4 - Particularly high corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Temperature of medium	-50 °C...60 °C
Ambient temperature	-50 °C...60 °C
Product weight	390 g
Note on materials	RoHS-compliant
Seals material	NBR VMQ
Housing material	Aluminum, ematal coated High-alloy stainless steel