


Quarter turn actuator DSRL-10-180-P-FW

Part number: 33296

FESTO



Data sheet

Feature	Value
Size	10
Cushioning angle	2.4 deg
Adjustment range of swivel angle	0 deg...180 deg
Swivel angle	0 deg...180 deg
Cushioning	Elastic cushioning rings/pads at both ends
Mounting position	Any
Mode of operation	Double-acting
Structural design	Rotary vane
Position sensing	None
Operating pressure	2.5 bar...8 bar
Max. swivel frequency at 6 bar	3 Hz
Operating medium	Compressed air as per ISO 8573-1:2010 [7::-]
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-10 °C...60 °C
Theoretical torque at 6 bar	0.5 Nm
Product weight	100 g
Type of mounting	With through-hole
Pneumatic connection	M3
Drive shaft material	Steel Nickel-plated
Seals material	NBR