

Clevis foot
LBG-50
Part number: 31763



Data sheet

Feature	Value
Size	50
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Suitability for the production of Li-ion batteries	Metals with more than 5% by mass of copper are excluded from use. Exception are printed circuit boards, cables, electrical connectors and coils
Ambient temperature	-40 °C...150 °C
Max. load capacity	2.5 kN
Product weight	540 g
	19.03 oz
Note on materials	RoHS-compliant
Mounting material	Cast stainless steel
Bolt material	Case-hardened steel
Fuse material	Spring steel