


Guide unit EAGF-P1-KF-16-100

Part number: 3192934

FESTO



Data sheet

Feature	Value
Size	16
Stroke	100 mm
Reversing backlash	0 µm
Mounting position	Any
Guide	Recirculating ball bearing guide
Structural design	Guide
Max. acceleration	25 m/s ²
Max. speed	1 m/s
Corrosion resistance class (CRC)	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Degree of protection	IP40
Ambient temperature	0 °C...50 °C
Max. force Fy	160 N
Max. force Fy static	355 N
Max. force Fz	160 N
Max. force Fz static	355 N
Max. torque Mx	6 Nm
Max. static moment Mx	13 Nm
Max. torque My	4 Nm
Max. static moment My	9 Nm
Max. torque Mz	4 Nm
Max. static moment Mz	9 Nm
Displacement force	3.2 N
Moving mass at 0 mm stroke	160 g
Basic weight with 0 mm stroke	600 g
Additional weight per 10 mm stroke	8 g
Additional moving mass per 10 mm stroke	8 g
Center of gravity of moving mass with 0 mm stroke	29 mm
Center of gravity of moving mass with 10 mm stroke	4.5 mm
Type of mounting	With internal thread
Note on materials	RoHS-compliant

Feature	Value
Material of guide component	Tempered steel Hard-chrome-plated
Housing material	Wrought aluminum alloy Anodized
Material of yoke plate	Wrought aluminum alloy Anodized