


# Trunnion support LNZG-100/125

Part number: 32962

FESTO



## Data sheet

Feature	Value
Size	100/125
Based on norm	ISO 15552
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Suitability for the production of Li-ion batteries	Product corresponds to Festo's internal product definition for use in battery production:Metals with more than 1% by mass of copper, zinc or nickel are excluded from use.The exceptions are nickel in steel, chemically nickel-plated surfaces, circuit boards, cables, electrical plug connectors and coils
Ambient temperature	-40 °C...80 °C
Max. load capacity	9 kN
Product weight	306 g
Note on materials	RoHS-compliant
Mounting material	Wrought aluminum alloy
Material of bearing	Polymer