


Sensor box SRBG-C1-N-1-ZU-M12

Part number: 3568056

FESTO



Data sheet

Feature	Value
Design	Rectangular
Based on norm	EN 60947-5-2 VDI/VDE 3845
Certification	CCC RCM compliance mark c UL us (OL)
CE marking (see declaration of conformity)	As per EU EMC directive As per EU RoHS directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC To UK RoHS instructions
KC characters	KC EMC
Certificate issuing authority	2024010305706390
Note on materials	RoHS-compliant
Measuring principle	Inductive
Ambient temperature	-25 °C...70 °C
Switching output	Non-contact, 2-wire
Switching element function	N/O contact
Max. switching frequency	500 Hz
Max. output current DC	100 mA
Voltage drop	6 V
Minimum load current	4 mA
Residual current	0 mA...1 mA
DC operating voltage range	6 V...60 V
Reverse polarity protection	for all electrical connections
Electrical connection, input	M12x1
Electrical connection 1, connection type	Plug
Electrical connection 1, cable outlet	Straight
Electrical connection 1, design	Round
Electrical connection 1, connection technology	M12x1 A-coded as per EN 61076-2-101
Electrical connection 1, number of pins/wires	4
Type of mounting	Threaded
Mounting position	Any

Feature	Value
Product weight	70 g
Housing material	PBT
Material of screws	High-alloy stainless steel
Material of pneumatic fitting	Die-cast zinc, nickel-plated
Switching status indication	LED yellow
Storage temperature	-25 °C...70 °C
Degree of protection	IP67
Shock resistance	Shock test with severity level 2 as per FN 942017-5 and EN 60068-2-27
Vibration resistance	Transport application test with severity level 2 as per FN 942017-4 and EN 60068-2-6
LABS (PWIS) conformity	VDMA24364 zone III
Contamination level	3