

**Parallel kit**  
**EAMM-U-30-V20-28A-44**  
Part number: 4767125

**FESTO**



**Data sheet**

| Feature                   | Value                  |
|---------------------------|------------------------|
| Size                      | 30                     |
| Center-to-center distance | 44 mm                  |
| Mounting position         | Any                    |
| Gear ratio                | 1:1                    |
| Max. rotational speed     | 3000 rpm               |
| LABS (PWIS) conformity    | VDMA24364 zone III     |
| Storage temperature       | -20 °C...60 °C         |
| Relative air humidity     | 0 - 95 %               |
| Degree of protection      | IP40                   |
| Ambient temperature       | 0 °C...50 °C           |
| Mass moment of inertia    | 2.11 kgmm <sup>2</sup> |
| No-load driving torque    | 0.015 Nm               |
| Transferable torque       | 0.05 Nm                |
| Product weight            | 97 g                   |
| Interface code, actuator  | V20                    |
| Interface code, motor in  | 28A                    |
| Note on materials         | RoHS-compliant         |