

Compact air cylinder DPDM-10-10-S-PA

Part number: 4832117

FESTO



Data sheet

Feature	Value
Stroke	10 mm
Piston diameter	10 mm
Cushioning	Elastic cushioning rings/pads at both ends
Mounting position	Any
Mode of operation	Pushing Single-acting
Structural design	Piston Piston rod Profile barrel
Position sensing	For proximity sensor
Variants	Piston rod at one end
Operating pressure	0.2 MPa...0.8 MPa 2 bar...8 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Cleanroom class	Class 6 according to ISO 14644-1
Ambient temperature	-10 °C...80 °C
Theoretical force at 6 bar	38 N
Theoretical force at 6 bar, advancing	38 N
Moving mass at 0 mm stroke	6.8 g
Additional moving mass per 10 mm stroke	1 g
Basic weight with 0 mm stroke	30.5 g
Additional weight per 10 mm stroke	7.5 g
Type of mounting	With through-hole With internal thread Optionally:
Pneumatic connection	M5
Note on materials	RoHS-compliant
Cover material	Wrought aluminum alloy
Seals material	NBR TPE-U(PU)

Feature	Value
Housing material	Wrought aluminum alloy, anodized
Piston rod material	High-alloy stainless steel