

Compact air cylinder DPDM-6-5-PA

Part number: 4830900

FESTO



Data sheet

Feature	Value
Stroke	5 mm
Piston diameter	6 mm
Cushioning	Elastic cushioning rings/pads at both ends
Mounting position	Any
Mode of operation	Double-acting
Structural design	Piston Piston rod Profile barrel
Position sensing	For proximity sensor
Variants	Piston rod at one end
Operating pressure	0.18 MPa...0.8 MPa 1.8 bar...8 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Cleanroom class	Class 6 according to ISO 14644-1
Ambient temperature	-10 °C...80 °C
Theoretical force at 6 bar	17 N
Theoretical force at 6 bar, retracting	13 N
Theoretical force at 6 bar, advancing	17 N
Moving mass at 0 mm stroke	2.8 g
Additional moving mass per 10 mm stroke	0.6 g
Basic weight with 0 mm stroke	20.7 g
Additional weight per 10 mm stroke	6.3 g
Type of mounting	With through-hole With internal thread Optionally:
Pneumatic connection	M5
Note on materials	RoHS-compliant
Cover material	Wrought aluminum alloy
Seals material	NBR TPE-U(PU)

Feature	Value
Housing material	Wrought aluminum alloy, anodized
Piston rod material	High-alloy stainless steel