

Round cylinder DSNU-S-8-25-P-A-MQ

Part number: 5205900

FESTO



Data sheet

| Feature | Value |
|--|--|
| Stroke | 25 mm |
| Piston diameter | 8 mm |
| Piston rod thread | M4 |
| Cushioning | Elastic cushioning rings/pads at both ends |
| Mounting position | Any |
| Structural design | Piston Piston rod Cylinder barrel |
| Position sensing | For proximity sensor |
| Operating pressure | 0.15 MPa...1 MPa 1.5 bar...10 bar |
| Mode of operation | Double-acting |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Cleanroom class | Class 6 according to ISO 14644-1 |
| Ambient temperature | -20 °C...80 °C |
| Theoretical force at 6 bar, retracting | 22.6 N |
| Theoretical force at 6 bar, advancing | 30.2 N |
| Moving mass at 0 mm stroke | 6.3 g |
| Additional moving mass per 10 mm stroke | 1 g |
| Basic weight with 0 mm stroke | 20 g |
| Additional weight per 10 mm stroke | 2.4 g |
| Type of mounting | With accessories |
| Pneumatic connection | M5 |
| Note on materials | RoHS-compliant |
| Cover material | Wrought aluminum alloy, anodized |
| Seals material | TPE-U(PU) |
| Piston rod material | High-alloy stainless steel |
| Material of cylinder barrel | High-alloy stainless steel |