

# Servo motor EMMT-AS-60-L-LS-RS

Part number: 5242212

**FESTO**



## Data sheet

| Feature                                                             | Value                                                                                                                                                |
|---------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------|
| Ambient temperature                                                 | -15 °C...40 °C                                                                                                                                       |
| Note on ambient temperature                                         | Up to 80 °C with derating of -1.5% per degree Celsius                                                                                                |
| Max. installation height                                            | 4000 m                                                                                                                                               |
| Information on max. installation height                             | with 1,000 m and longer only with derating of -1.0% per 100 m                                                                                        |
| Storage temperature                                                 | -20 °C...70 °C                                                                                                                                       |
| Relative air humidity                                               | 0 - 90 %                                                                                                                                             |
| Conforms to standard                                                | IEC 60034                                                                                                                                            |
| Thermal class according to EN 60034-1                               | F                                                                                                                                                    |
| Max. winding temperature                                            | 155 °C                                                                                                                                               |
| Rating class according to EN 60034-1                                | S1                                                                                                                                                   |
| Temperature monitoring                                              | Digital motor temperature transmission via EnDat® 2.2                                                                                                |
| Motor type as per EN 60034-7                                        | IM B5<br>IM V1<br>IM V3                                                                                                                              |
| Mounting position                                                   | Any                                                                                                                                                  |
| Degree of protection                                                | IP40                                                                                                                                                 |
| Note on degree of protection                                        | IP40 for motor shaft without rotary shaft seal<br>IP65 for motor shaft with rotary shaft seal<br>IP67 for motor housing, incl. connection technology |
| Concentricity, coaxiality, axial runout according to DIN SPEC 42955 | N                                                                                                                                                    |
| Balancing quality                                                   | G 2.5                                                                                                                                                |
| Detent torque                                                       | <1.0% of peak torque                                                                                                                                 |
| Bearing lifetime, under nominal conditions                          | 20000 h                                                                                                                                              |
| Interface code, motor out                                           | 60P                                                                                                                                                  |
| Electrical connection 1, connection type                            | Hybrid plug                                                                                                                                          |
| Electrical connection 1, connection technology                      | M23x1                                                                                                                                                |
| Electrical connection 1, number of pins/wires                       | 15                                                                                                                                                   |
| Contamination level                                                 | 2                                                                                                                                                    |
| Note on materials                                                   | RoHS-compliant                                                                                                                                       |
| Corrosion resistance class (CRC)                                    | 0 - No corrosion stress                                                                                                                              |

| Feature                                                      | Value                                                                                                |
|--------------------------------------------------------------|------------------------------------------------------------------------------------------------------|
| LABS (PWIS) conformity                                       | VDMA24364 zone III                                                                                   |
| Vibration resistance                                         | Transport application test with severity level 2 as per FN 942017-4 and EN 60068-2-6                 |
| Shock resistance                                             | Shock test with severity level 2 as per FN 942017-5 and EN 60068-2-27                                |
| Certification                                                | RCM compliance mark<br>c UL us - Recognized (OL)                                                     |
| CE marking (see declaration of conformity)                   | As per EU EMC directive<br>As per EU low voltage directive<br>As per EU RoHS directive               |
| UKCA marking (see declaration of conformity)                 | To UK instructions for EMC<br>To UK RoHS instructions<br>To UK instructions for electrical equipment |
| Certificate issuing authority                                | UL E342973                                                                                           |
| Nominal operating voltage DC                                 | 325 V                                                                                                |
| Type of winding switch                                       | Star inside                                                                                          |
| Number of pole pairs                                         | 5                                                                                                    |
| Stall torque                                                 | 1.66 Nm                                                                                              |
| Nominal torque                                               | 1.4 Nm                                                                                               |
| Peak torque                                                  | 5.6 Nm                                                                                               |
| Nominal rotary speed                                         | 3000 rpm                                                                                             |
| Max. rotational speed                                        | 6800 rpm                                                                                             |
| Max. mechanical speed                                        | 16000 rpm                                                                                            |
| Angular acceleration                                         | 100000 rad/s <sup>2</sup>                                                                            |
| Motor nominal power                                          | 440 W                                                                                                |
| Continuous stall current                                     | 3.8 A                                                                                                |
| Motor nominal current                                        | 3.2 A                                                                                                |
| Peak current                                                 | 18.3 A                                                                                               |
| Motor constants                                              | 0.44 Nm/A                                                                                            |
| Standstill torque constant                                   | 0.52 Nm/A                                                                                            |
| Voltage constant, phase-to-phase                             | 31.2 mVmin                                                                                           |
| Phase-phase winding resistance                               | 2.68 Ohm                                                                                             |
| Winding inductance phase-phase                               | 12 mH                                                                                                |
| Winding longitudinal inductivity Ld (phase)                  | 5 mH                                                                                                 |
| Cross inductivity Lq (phase)                                 | 6 mH                                                                                                 |
| Electric time constant                                       | 3 ms                                                                                                 |
| Thermal time constant                                        | 43 min                                                                                               |
| Thermal resistance                                           | 1 K/W                                                                                                |
| Measuring flange                                             | 250 x 250 x 15 mm, steel                                                                             |
| Total output inertia moment                                  | 0.403 kgcm <sup>2</sup>                                                                              |
| Product weight                                               | 1910 g                                                                                               |
| Permissible axial shaft load                                 | 70 N                                                                                                 |
| Permissible radial shaft load                                | 350 N                                                                                                |
| Rotor position sensor                                        | Absolute encoder, single-turn                                                                        |
| Rotor position sensor for manufacturer designation           | ECI 1118                                                                                             |
| Rotor position encoder for absolutely detectable revolutions | 1                                                                                                    |
| Rotor position sensor interface                              | EnDat® 22                                                                                            |
| Rotor position sensor measuring principle                    | Inductive                                                                                            |
| Rotor position encoder for DC operating voltage              | 5 V                                                                                                  |
| Rotor position encoder for DC operating voltage range        | 3.6 V...14 V                                                                                         |
| Rotor position encoder for positional values per revolution  | 262144                                                                                               |
| Rotor position sensor resolution                             | 18 bit                                                                                               |
| Rotor position encoder system accuracy angle measurement     | -120 arcsec...120 arcsec                                                                             |
| MTTF, subcomponent                                           | 190 years, rotor position sensor                                                                     |