

# Round cylinder DSNU-S-8-15-P-A-MQ

Part number: 5205898

**FESTO**



## Data sheet

| Feature                                  | Value  |
|--|--|
| Stroke                                   | 15 mm  |
| Piston diameter                          | 8 mm   |
| Piston rod thread                        | M4   |
| Cushioning                               | Elastic cushioning rings/pads at both ends                         |
| Mounting position                        | Any  |
| Structural design                        | Piston<br>Piston rod<br>Cylinder barrel                            |
| Position sensing                         | For proximity sensor   |
| Operating pressure                       | 0.15 MPa...1 MPa<br>1.5 bar...10 bar                               |
| Mode of operation                        | Double-acting  |
| Operating medium                         | Compressed air as per ISO 8573-1:2010 [7:4:4]                      |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC)         | 2 - Moderate corrosion stress                                      |
| LABS (PWIS) conformity                   | VDMA24364-B2-L   |
| Cleanroom class                          | Class 6 according to ISO 14644-1                                   |
| Ambient temperature                      | -20 °C...80 °C   |
| Theoretical force at 6 bar, retracting   | 22.6 N   |
| Theoretical force at 6 bar, advancing    | 30.2 N   |
| Moving mass at 0 mm stroke               | 6.3 g  |
| Additional moving mass per 10 mm stroke  | 1 g  |
| Basic weight with 0 mm stroke            | 20 g   |
| Additional weight per 10 mm stroke       | 2.4 g  |
| Type of mounting                         | With accessories   |
| Pneumatic connection                     | M5   |
| Note on materials                        | RoHS-compliant   |
| Cover material                           | Wrought aluminum alloy, anodized                                   |
| Seals material                           | TPE-U(PU)  |
| Piston rod material                      | High-alloy stainless steel   |
| Material of cylinder barrel              | High-alloy stainless steel   |