



Motor cable
NEBM-H6G4-K-7.5-Q13N-LE4
Part number: 5219195

FESTO



Data sheet

| Feature | Value |
|--|--|
| Cable designation | Without label holder |
| Electrical connection 1, function | Field device end |
| Electrical connection 1, design | Rectangular |
| Electrical connection 1, connection type | Socket |
| Electrical connection 1, cable outlet | Straight |
| Electrical connection 1, connection technology | Connection diagram H6, coded for motor |
| Electrical connection 1, number of pins/wires | 4 |
| Electrical connection 1, occupied pins/wires | 4 |
| Electrical connection 2, function | Control side |
| Electrical connection 2, connection type | Cable |
| Electrical connection 2, connection technology | Open end |
| Electrical connection 2, number of pins/wires | 4 |
| Electrical connection 2, occupied pins/wires | 4 |
| DC operating voltage range | 0 V...300 V |
| Operating voltage range AC | 0 V...300 V |
| Current rating at 40° C | 9.5 A |
| Surge resistance | 2 kV |
| Cable length | 7.5 m |
| Cable characteristic | Standard |
| Connector cable test conditions | Test conditions on request |
| Bending radius, fixed cable installation | 74 mm |
| Bending radius, flexible cable installation | 111 mm |
| Cable diameter | 7.4 mm |
| Cable design | 4 x 0.79 mm ² |
| Nominal conductor cross section | 0.79 mm ² AWG18 |
| Wire ends | Cable end sleeve |
| Degree of protection | IP20 |
| Note on degree of protection | In mounted state |
| Ambient temperature | -25 °C...90 °C |
| Ambient temperature with flexible cable installation | -25 °C...90 °C |

| Feature | Value |
|--|--|
| CE marking (see declaration of conformity) | As per EU low voltage directive As per EU RoHS directive |
| UKCA marking (see declaration of conformity) | To UK RoHS instructions To UK instructions for electrical equipment |
| LABS (PWIS) conformity | VDMA24364 zone III |
| Note on materials | RoHS-compliant |
| Contamination level | 3 |
| Corrosion resistance class (CRC) | 0 - No corrosion stress |
| Material of cable sheath | TPE-E |
| Color cable sheath | Black |
| Housing material | PA |
| Housing colour | White |
| Insulating sheath material | TPE-E |