


# Vacuum generator VN-07-H-T2-PI2-VI2-RO1

Part number: 526105

**FESTO**



## Data sheet

Feature	Value
Nominal width of Laval nozzle	0.7 mm
Width dimension	10 mm
Muffler construction type	Open
Mounting position	Any
Ejector characteristics	High vacuum Standard
Integrated function	Pneumatic muffer open
Structural design	T-shape
Operating pressure for max. suction rate	2.1 bar
Operating pressure	1 bar...8 bar
Operating pressure for max. vacuum	4.7 bar
Max. vacuum	88 %
Nominal operating pressure	6 bar
Max. suction rate with respect to atmosphere	16 l/min
Air supply time at nominal operating pressure	1.9 s
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication not possible
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Temperature of medium	0 °C...60 °C
Noise level at nominal operating pressure	64 dB(A)
Ambient temperature	0 °C...60 °C
Max. tightening torque	0.5 Nm
Product weight	13 g
Type of mounting	With through-hole With accessories
Pneumatic connection 1	M5
Pneumatic connection 3	Pneumatic muffer open
Vacuum connection	M5
Material of connecting thread	Wrought aluminum alloy, anodized
Note on materials	RoHS-compliant
Seals material	NBR

Feature	Value
Female nozzle material	POM
Housing material	POM-reinforced
Muffler material	PE
Material of jet nozzle	Wrought aluminum alloy