

Short-stroke cylinder ADVC-6-5-P

Part number: 526899

FESTO



Data sheet

Feature	Value
Stroke	5 mm
Piston diameter	6 mm
Cushioning	Elastic cushioning rings/pads at both ends
Mounting position	Any
Mode of operation	Double-acting
Structural design	Piston Piston rod
Position sensing	None
Operating pressure	0.15 MPa...0.8 MPa 1.5 bar...8 bar 21.75 psi...116 psi
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-20 °C...80 °C
Theoretical force at 6 bar, retracting	13 N
Theoretical force at 6 bar, advancing	17 N
Moving mass	1.2 g
Product weight	7 g
Type of mounting	With through-hole With accessories Optionally:
Pneumatic connection	M3
Note on materials	RoHS-compliant
Cover material	Wrought aluminum alloy Anodized
Seals material	NBR TPE-U(PU)
Housing material	Wrought aluminum alloy Anodized
Piston rod material	High-alloy steel