



# Service unit combination MSB6-1/2:H3N3M1-WP-Z

Part number: 530219

FESTO

Consisting of filter, pressure regulator, lubricator and wall mounting plate. 12 bar maximum output pressure, 5 µm filter, with pressure gauge, plastic bowl with plastic bowl guard, manual condensate drain, direction of flow: from right to left.



## Data sheet

| Feature                                 | Value  |
|---|--|
| Size                                    | 6  |
| Series                                  | MS   |
| Actuator lock                           | Rotary knob with lock with accessories, lockable   |
| Assembly position                       | Vertical +/- 5°  |
| Grade of filtration                     | 5 µm   |
| Condensate drain                        | manual rotary  |
| Design structure                        | Pressure regulator with gauge<br>Standard filter<br>Standard oil-mist lubricator                                 |
| Bowl guard                              | Plastic guard  |
| Pressure gauge                          | with pressure gauge  |
| Pressure control range                  | 1 ... 12 bar   |
| Inlet pressure 1                        | 1.5 ... 18 bar   |
| Standard nominal flow rate              | 4,400 l/min  |
| Operating medium                        | Filtered, unlubricated compressed air, 40 µm filtration<br>Filtered, lubricated compressed air, 40 µm filtration |
| Corrosion resistance classification CRC | 2  |
| Storage temperature                     | -10 ... 60 °C  |
| Air purity class at output              | 3.7.- per DIN ISO 8573-1   |
| Medium temperature                      | -10 ... 60 °C  |
| Ambient temperature                     | -10 ... 60 °C  |
| Product weight                          | 2,000 g  |
| Mounting type                           | with accessories   |
| Pneumatic connection, port 1            | G1/2   |
| Pneumatic connection, port 2            | G1/2   |
| Materials information, housing          | Aluminum die cast  |
| Materials information for bowl          | PC   |