

Air line lubricator

MS12-LOE

Part number: 535041

FESTO



Data sheet

Feature	Value
Size	12
Series	MS
Mounting position	Vertical +/- 5°
Structural design	Proportional standard oil mist lubricator
Operating pressure	1 bar...16 bar
Minimum flow rate for lubricator function	400 l/min
Operating medium	Compressed air as per ISO 8573-1:2010 [:::-]
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Storage temperature	-10 °C...60 °C
Oil viscosity	ISO VG 32
Ambient temperature	0 °C...60 °C
Type of mounting	Line installation With accessories Optionally:
Housing material	Die-cast aluminum
Material of bowl	Wrought aluminum alloy