

Fine filter
MS12-LFM
Part number: 535042

FESTO



Data sheet

Feature	Value
Series	MS
Size	12
Structural design	Fiber filter
Condensate drain	Fully automatic Fully automatic, electrically controlled Manual, non-detenting Manually rotating
Operating pressure	0.08 MPa...2 MPa 0.8 bar...20 bar 11.6 psi...290 psi
Operating medium	Compressed air as per ISO 8573-1:2010 [6::4] Inert gas
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Temperature of medium	-10 °C...60 °C
Ambient temperature	-10 °C...60 °C
Storage temperature	-10 °C...60 °C
Type of mounting	Line installation With accessories Optionally:
Mounting position	Vertical +/- 5°
Housing material	Die-cast aluminum
Compressed air filter material	Borosilicate fiber
Material of bowl	Wrought aluminum alloy
Note on materials	RoHS-compliant