

# Compressed air filter MS4N-LF-1/4-EUM

Part number: 535692

**FESTO**



## Data sheet

Feature	Value
Size	4
Series	MS
Mounting position	Vertical +/- 5°
Grade of filtration	40 µm
Condensate drain	Manually rotating
Structural design	Sinter filter with centrifugal separator
Bowl guard	Integrated as metal bowl guard
Degree of condensate separation	75 %
Operating pressure	0 bar...14 bar
Standard nominal flow rate	1700 l/min
Operating medium	Compressed air as per ISO 8573-1:2010 [::9:-] Inert gas
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Storage temperature	-10 °C...60 °C
For use in the food industry	See supplementary material information
Air quality class at the output	Compressed air as per ISO 8573-1:2010 [7:8:4]
Temperature of medium	-10 °C...60 °C
Ambient temperature	-10 °C...60 °C
Pore size	40 µm
Product weight	349 g
Type of mounting	Line installation With accessories Optionally:
Pneumatic connection 1	1/4 NPT
Pneumatic connection 2	1/4 NPT
Note on materials	RoHS-compliant
Material of sub-base	Die-cast aluminum
Seals material	NBR
Compressed air filter material	PE
Housing material	Die-cast aluminum

Feature	Value
Material of bowl	Die-cast aluminum Wrought aluminum alloy
Inspection window material	PA
Separating disc material	POM