



# Air solenoid valve

## MFH-3-1/2-EX

Part number: 535899

**FESTO**



## Data sheet

| Feature   | Value   |
|---|---|
| Valve function                                    | 3/2, closed, monostable                         |
| Actuation type                                    | Electrical                                      |
| Width   | 52 mm   |
| Standard nominal flow rate                        | 3700 l/min                                      |
| Pneumatic working port                            | G1/2  |
| Operating voltage                                 | Via solenoid coil, to be ordered separately     |
| Operating pressure                                | 0.15 MPa...0.8 MPa<br>1.5 bar...8 bar           |
| Structural design                                 | Plate seat                                      |
| Reset method                                      | Mechanical spring                               |
| CE marking (see declaration of conformity)        | as per EU explosion protection directive (ATEX) |
| Explosion protection certification outside the EU | EPL Db (GB)<br>EPL Gb (GB)                      |
| UKCA marking (see declaration of conformity)      | acc. to UK EX instructions                      |
| ATEX category gas                                 | II 2G   |
| ATEX category for dust                            | II 2D   |
| Type of ignition protection for gas               | Ex h IIC T4 Gb                                  |
| Type of (ignition) protection for dust            | Ex h IIIC T130°C Db                             |
| Explosive ambient temperature                     | -5°C ≤ Ta ≤ +40°C                               |
| Degree of protection                              | IP65  |
| Nominal width                                     | 14 mm   |
| Width dimension                                   | 69 mm   |
| Exhaust air function                              | With flow control option                        |
| Sealing principle                                 | Soft  |
| Mounting position                                 | Any   |
| Manual override                                   | Detenting                                       |
| Type of control                                   | Pilot-controlled                                |
| Flow direction                                    | Non-reversible                                  |
| Lap   | Underlap  |
| b-value   | 0.3   |
| Switching time off                                | 90 ms   |
| On switching time                                 | 18 ms   |

| Feature                                  | Value   |
|--|---|
| Max. positive test pulse with 0 signal   | 2200 µs   |
| Max. negative test pulse on 1 signal     | 3700 µs   |
| Coil characteristics                     | See solenoid coil, to be ordered separately   |
| Explosion prevention and protection      | Zone 1 (ATEX)<br>Zone 1 (UKEX)<br>Zone 2 (ATEX)<br>Zone 21 (ATEX)<br>Zone 21 (UKEX)<br>Zone 22 (ATEX) |
| Operating medium                         | Compressed air as per ISO 8573-1:2010 [7:4:4]   |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use)                                    |
| Corrosion resistance class (CRC)         | 1 - Low corrosion stress  |
| LABS (PWIS) conformity                   | VDMA24364-B1/B2-L   |
| Storage temperature                      | -20 °C...60 °C  |
| Temperature of medium                    | -5 °C...40 °C   |
| Ambient temperature                      | -5 °C...40 °C   |
| Product weight                           | 1100 g  |
| Electrical connection                    | Via F coil, to be ordered separately  |
| Type of mounting                         | On terminal strip<br>With through-hole<br>Optionally:   |
| Venting hole connection                  | M5  |
| Pilot exhaust air port 82                | M5  |
| Pneumatic connection 1                   | G1/2  |
| Pneumatic connection 2                   | G1/2  |
| Pneumatic connection 3                   | G1/2  |
| Note on materials                        | RoHS-compliant  |
| Seals material                           | NBR   |
| Housing material                         | Die-cast aluminum   |