

Quarter turn actuator DAPS-0015-090-RS2-F0305

Part number: 533428

FESTO



Data sheet

| Feature | Value |
|--|--|
| Size of valve actuator | 0015 |
| Flange hole pattern | F03 F05 |
| Swivel angle | 90 deg |
| End-position adjusting range at 0° | -1 deg...9 deg |
| End-position adjusting range at nominal swivel angle | 81 deg...91 deg |
| Depth shaft connection | 13.2 mm |
| Information on the end-position adjusting range | One end position optionally adjustable |
| Standard connection for valve | ISO 5211 |
| Cushioning | No cushioning |
| Mounting position | Any |
| Mode of operation | Single-acting |
| Structural design | Scotch yoke system |
| Position sensing | None |
| Closing direction | Clockwise closing |
| Valve connection conforms to standard | VDI/VDE 3845 (NAMUR) |
| Safety integrity level (SIL) | Up to SIL 2 low demand mode |
| Connection pressure for spring force | 0.35 MPa 3.5 bar |
| Operating pressure | 0.35 MPa...0.84 MPa 3.5 bar...8.4 bar |
| Nominal operating pressure | 0.56 MPa 5.6 bar |
| Max. swivel frequency at 6 bar | 1 Hz |
| CE marking (see declaration of conformity) | as per EU explosion protection directive (ATEX) |
| UKCA marking (see declaration of conformity) | acc. to UK EX instructions |
| Explosion prevention and protection | Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX) |
| Certificate issuing authority | German Technical Control Board North (TÜV Nord) 212170801 |
| ATEX category gas | II 2G |
| ATEX category for dust | II 2D |

| Feature | Value |
|---|---|
| Type of ignition protection for gas | Ex h IIC T6...T3 Gb X |
| Type of (ignition) protection for dust | Ex h IIIC T85°C...T200°C Db X |
| Explosive ambient temperature | -20°C ≤ Ta ≤ +60°C |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC) | 3 - High corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Ambient temperature | -20 °C...80 °C |
| Torque at nominal operating pressure and 0° swivel angle | 18.8 Nm |
| Torque at nominal operating pressure and 50° swivel angle | 10.3 Nm |
| Torque at nominal operating pressure and 90° swivel angle | 15.7 Nm |
| Note about the torque | The actuator's operating torque must not be higher than the maximum permissible torque listed in ISO 5211, based on the size of the mounting flange and the coupling. |
| Spring return torque at 0° swivel angle | 6.3 Nm |
| Spring return torque with 50° swivel angle | 4.7 Nm |
| Spring return torque with 90° swivel angle | 9.4 Nm |
| Spring force | 2 |
| Air consumption at 6 bar per cycle 0°-nominal swivel angle-0° | 0.63 l |
| Product weight | 1200 g |
| Shaft connection | T11 |
| Pneumatic connection | G1/8 |
| Note on materials | RoHS-compliant |
| Cover material | Wrought aluminum alloy |
| Seals material | FPM NBR PUR |
| Housing material | Wrought aluminum alloy |
| Material of screws | High-alloy steel |
| Shaft material | High-alloy steel |
| Material number for shaft | 1.4305 |