

Pick and place machine HSP-12-AS

Part number: 533605

FESTO



Data sheet

Feature	Value
Size	12
Y-stroke	52 mm...68 mm
Z-stroke	20 mm...30 mm
Z working stroke	15 mm
Cushioning	Pneumatic shock absorber at both ends Soft characteristic curve
Mounting position	Guide rail Vertical
Structural design	Actuator shaft Cross guide Positively driven motion sequence
Position sensing	For proximity sensor
Protection against torsion/guide	Cross guide
Minimum cycle time	0.6 s
Repetition accuracy	±0.01 mm
Operating medium	Compressed air as per ISO 8573-1:2010 [7:::]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	0 °C...60 °C
Max. driving torque on actuator shaft	1.25 Nm
Max. axial force at actuator shaft	18 N
Max. torque Mx dynamic	1.1 Nm
Max. static moment Mx	5 Nm
Max. torque My dynamic	1.1 Nm
Max. static moment My	5 Nm
Max. torque Mz dynamic	1.1 Nm
Max. static moment Mz	5 Nm
Max. payload	0.5 kg
Max. radial force on actuator shaft	45 N
Theoretical force at 6 bar	40 N
Product weight	1800 g
Front unit mounting	With through-hole

Feature	Value
Type of mounting	With through-hole With slot nuts
Base plate material	Wrought aluminum alloy
Cross guide material	Tempered steel
Side covers material	Wrought aluminum alloy