


Active carbon filter

MS4-LFX-1/4-U

Part number: 535782

FESTO



Data sheet

Feature	Value
Size	4
Series	MS
Mounting position	Vertical +/- 5°
Structural design	Active carbon filter
Bowl guard	Integrated as metal bowl guard
Operating pressure	0 bar...14 bar
Max. standard flow rate for air quality class	360 l/min
Operating medium	Druckluft nach ISO 8573-1:2010 [3:4:2]
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Storage temperature	-10 °C...60 °C
Air quality class at the output	Druckluft nach ISO 8573-1:2010 [3:4:1]
Temperature of medium	5 °C...30 °C
Residual oil content	0.003 mg/m³
Ambient temperature	-10 °C...60 °C
Product weight	350 g
Type of mounting	Line installation With accessories Optionally:
Pneumatic connection 1	G1/4
Pneumatic connection 2	G1/4
Note on materials	RoHS-compliant
Compressed air filter material	Activated carbon
Housing material	Die-cast aluminum
Material of bowl	Die-cast aluminum Wrought aluminum alloy
Inspection window material	PA