


Pneumatic valve VL/O-3-1/2-EX

Part number: 536030

FESTO



Data sheet

Feature	Value
Valve function	3/2, open/closed, monostable
Actuation type	Pneumatic
Width	52 mm
Standard nominal flow rate	3700 l/min
Pneumatic working port	G1/2
Operating pressure	-0.095 MPa...1 MPa -0.95 bar...10 bar
Structural design	Plate seat
Reset method	Mechanical spring
CE marking (see declaration of conformity)	as per EU explosion protection directive (ATEX)
UKCA marking (see declaration of conformity)	acc. to UK EX instructions
ATEX category gas	II 2G
ATEX category for dust	II 2D
Type of ignition protection for gas	Ex h IIC T4 Gb
Type of (ignition) protection for dust	Ex h IIIC T130°C Db
Explosive ambient temperature	-10°C ≤ Ta ≤ +60°C
Explosion protection certification outside the EU	EPL Db (GB) EPL Gb (GB)
Nominal width	14 mm
Width dimension	69 mm
Exhaust air function	With flow control option
Sealing principle	Soft
Mounting position	Any
Manual override	None
Type of control	Direct
Pilot air supply port	External
Flow direction	Reversible
Lap	Underlap
Pilot pressure MPa	0.1 MPa...1 MPa
Pilot pressure	1 bar...10 bar
b-value	0.3
Switching time off	30 ms

Feature	Value
On switching time	17 ms
Explosion prevention and protection	Zone 1 (ATEX) Zone 1 (UKEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 21 (UKEX) Zone 22 (ATEX)
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Storage temperature	-20 °C...60 °C
Temperature of medium	-10 °C...60 °C
Pilot medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Ambient temperature	-10 °C...60 °C
Product weight	860 g
Type of mounting	On terminal strip With through-hole Optionally:
Venting hole connection	M5
Pilot air port 110	G1/4
Pilot air port 12	G1/4
Pneumatic connection 1	G1/2
Pneumatic connection 11	G1/2
Pneumatic connection 2	G1/2
Pneumatic connection 3	G1/2
Pneumatic connection 33	G1/2
Note on materials	RoHS-compliant
Seals material	NBR
Housing material	Die-cast aluminum