



Transmitter

SOEG-S-M18W-K-L

Part number: 537693

FESTO



Data sheet

Feature	Value
Design	Round
Conforms to standard	EN 60947-5-2
Certification	RCM compliance mark c UL us - Listed (OL)
CE marking (see declaration of conformity)	As per EU EMC directive
Measured variable	Position
Measuring principle	Optoelectronic
Method of measurement	Through-beam sensor Transmitter
Type of light	Red
Working range	20000 mm
Ambient temperature	-25 °C...55 °C
Voltage drop	2 V
Short-circuit protection	Pulsed
DC operating voltage range	10 V...36 V
Residual ripple	20 %
Idle current	15 mA
Reverse polarity protection	for all electrical connections
Electrical connection	3-wire Cable
Cable length	2.5 m
Material of cable sheath	TPE-U(PUR)
Size	M18x1
Type of mounting	With lock nut
Tightening torque	20 Nm
Product weight	124 g
Housing material	Brass Chrome-plated
Material of union nut	Brass Chrome-plated
Ambient temperature with flexible cable installation	-5 °C...55 °C
Degree of protection	IP65 IP67

Feature	Value
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L